


SmallRig



RA-D55 / RA-D85 / RA-D120

Parabolic Softbox

User Manual

Thank you for purchasing SmallRig RA-D55 / RA-D85 / RA-D120 Parabolic Softbox.


SmallRig RA-D55 / RA-D85 / RA-D120 Parabolic Softboxes are a kind of versatile soft light accessory with 55cm / 85cm / 120cm diameter. Universal Bowens Mount design, makes it compatible with SmallRig RC 120D / RC 120B / RC 220D / RC 220B / RC 350D / RC 350B / RC 450D / RC 450B and other Bowens Mount Light of other brands.

The new generation of self-developed quick-release design, the diffusion and the frame are combined into one, you can easily assemble and disassemble the dome in 15 seconds, simplifying the use process, bringing you the best user experience.


RA-D55 / RA-D85 / RA-D120 also Include a high-quality fabric grid to help focus in your light beam angle to 45 degrees, which will allow you to maximize control of your lighting.

The Parabolic Softboxes Adopt industrial-grade soft material and highly reflective coating with two diffusions for a stronger soft effect or higher light transmission to satisfy your different needs.


In the Box




Softbox × 1



Honeycomb Grid × 1




Internal Diffusion × 1



External Diffusion × 1



Carrying Bag × 1



User Manual × 1

Installation & Removal



1, Method 1: Put the softbox on the flat ground and press it open with both hands.



2, Method 2: Press the chassis diagonally and pull it up respectively, and make it enter the fixed clamping position with a "click" sound.



3. Paste the internal diffusion onto the Velcro buckle on the softbox.



4. Paste the external diffusion onto the black Velcro tape on the edge of the softbox.



5. Paste the honeycomb grid onto the black Velcro tape on the edge of the softbox.



6. Disassembly: gently lift the skeleton, press it to complete disassembly.

Specifications

Product Name	RA-D55 Parabolic Softbox
Opening Softbox Size	Φ550 × 370mm (21.6 × 14.6")
External Diffusion Size	Φ530mm (20.9")
Internal Diffusion Size	Φ400mm (15.7")
Honeycomb Grid Size	Φ540mm (21.3")
Product Weight	1120g / 2.47lbs

Product Name	RA-D85 Parabolic Softbox
Opening Softbox Size	Φ840 × 570mm (33.1 × 22.4")
External Diffusion Size	Φ830mm (32.7")
Internal Diffusion Size	Φ645mm (25.4")
Honeycomb Grid Size	Φ830mm (32.7")
Product Weight	1494g / 3.29lbs

Product Name	RA-D120 Parabolic Softbox
Opening Softbox Size	Φ1190 × 710mm (46.8 × 27.9")
External Diffusion Size	Φ1180mm (46.5")
Internal Diffusion Size	Φ890mm (35")
Honeycomb Grid Size	Φ1180mm (46.5")
Product Weight	2590g / 5.7lbs

If any change in technology parameters, shall take real product as criterion. No inform will be made.